



# TECHNICAL DATA SHEET OF savE® OM50

savE® Phase Change Materials (PCM) are organic or inorganic Chemical Compound that have large amount of heat energy stored in the form of Latent Heat which is absorbed or released when the materials Change state from solid to liquid or liquid to solid. The PCM retains its latent heat without any Change in physical or chemical properties over thousands of Cycles. Various specific temperature PCM's are commercially available in the market (varying between -35°C to 90°C) depending upon the applications.

## Applications

**PCM provides energy efficient solutions for many industries including:**

- Insulation for Building and Piping Products
- Biopharmaceutical Transportation
- Telecommunications and Heat Sinks
- Hot and Cold Storage
- Food / Poultry / Milk Products Transportation
- Boiler and Hot Water Systems Industry looking to exploit Off-Peak Electricity Tariffs / Reducing Chilling Equipment Costs by Storing Energy at Off-Peak Hours

However there is no limit as to who can apply PCM technology to their operation, to improve thermal management, Cost and energy efficiencies.

## PLUS® Encapsulation

PLUS® pioneered the use of HDPE panels as encapsulation for PCMs in India. Our Calculations for total heat transfer across thin membranes show that HDPE / PP is as good as aluminum, stainless steel, etc. Plus® encapsulations are thin enough to give good overall heat transfer Coefficient as good as many metals with better mechanical strength.

## savE® OM50

savE® OM50 is an organic Chemical based PCM having nominal melting temperature of 50°C. It stores thermal energy as latent heat in its crystalline form. On Changing phase this latent heat is released or absorbed, allowing the ambient temperature within the system to be maintained. OM50 is constituted of the right mix of various additives allowing equilibrium between solid and liquid phases to be attained at the melting point. Also OM50 is free flowing in molten state and can be encapsulated in various forms.

## Why savE® OM50?

savE® OM50 has a nominal phase Change temperature of 50°C, a temperature that makes it ideal for many Heating/cooling thermal energy applications. Some of its salient features include:

### Pluss Advanced Technologies Pvt. Ltd.

610-A Udyog Vihar, Phase V, Gurgaon - 122016 (Haryana), India

Telephone: +91 - 124 - 4309490/91/92


E-mail: [info@pluss.co.in](mailto:info@pluss.co.in) | Web: [www.pluss.co.in](http://www.pluss.co.in)

- OM50 is chemically and thermally stable by using Pluss® proprietary additives.
- This is mixture of organic fatty acids.

**Technical Specification:**

Product : savE®  
 Series : OM50  
 Description : Mixture of organic materials  
 Appearance : White Color Waxy Solid below 50°C

**T-History Test**



**Fig1: T-History graph for OM50 done in water bath**

A 20g sample is taken in a test tube in molten Condition and placed in a temperature Controlled bath. A temperature sensor is placed in the test tube and bath to record the temperatures using a data logger. The bath is maintained at 40°C during the freezing Cycle and at around 60°C during the melting Cycle.

| Property                           | Value*  | Test Method      | Test Conditions (if any) |
|------------------------------------|---------|------------------|--------------------------|
| Melting Temp (°C)                  | 50.3    | PLUSS® T-History | @ 60 °C Liquid Bath      |
| Freezing Temp (°C)                 | 50      | PLUSS® T-History | @ 40 °C Liquid Bath      |
| Latent Heat (kJ/kg)                | 250     | PLUSS® T-History | @ 45 to 55 °C            |
| Liquid Density (kg/m³)             | NA      |                  |                          |
| Solid Density (kg/m³)              | 850     | PLUSS® Internal  | @ 30°C                   |
| Liquid Specific Heat (kJ/kgK)      | 3.05    | Calorimeter      | @ 60 °C                  |
| Solid Specific Heat (kJ/kgK)       | NA      |                  |                          |
| Liquid Thermal Conductivity (W/mK) | 0.14    | KD2Pro           | @ 60 °C                  |
| Solid Thermal Conductivity (W/mK)  | 0.21    | KD2Pro           | @ 30 °C                  |
| Base Material                      | Organic |                  |                          |
| Congruent Melting                  | Yes     |                  |                          |
| Flammability                       | No      |                  |                          |
| Thermal Stability (Cycles)         | ~2000   | PLUSS® Internal  |                          |
| Maximum Operating Temperature (°C) | 120     |                  |                          |
| Flash Point (°C)                   | 200     |                  |                          |

\* Nominal Values. Actual values mentioned in Test Certificate

The information given here is meant as a guide to determining suitability of our products for the stated applications. It is based on trials carried out by our laboratories and data selected from literature and shall in no event be held to constitute or imply any warranty. The products are intended for use in industrial applications. The users should test the materials before use and satisfy themselves with regard to contents and suitability in the desired application. Our formal specifications define the limits of our commitment. Recommendation herein may not be construed as freedom to infringe/operate under any third party patents. In the event of a proven claim, our liability is limited only to replacement of our material and in no case shall we be liable for special, incidental or consequential damages arising out of usage of our material. This datasheet is subject to change without notice.