OPTIM® GE-344 Speciality Polymers

TECHNICAL DATA SHEET

OPTIM® GE-344 is a glycidyl methacrylate modified ultra-low density polyethylene. It is used for toughening of Polycarbonates and Polyesters such as PET & PBT.

Applications

- Impact modifier for full range of filled and unfilled PC, PET & PBT. Level of improvement obtained is a function of the OPTIM® GE-344 addition level.
- Scrap upgradation of PC, PBT and PC/PBT blends.
- Chemical coupling agent for mineral and glass fillers in PET & PBT compounds.
- Useful for low temperature applications.

Key Properties

General	Typical Value (SI)	Test Method
MFI (190 °C/2.16 Kg)	3.5 g/10min	ASTM D1238
Density	0.870 g/cm3	ASTM D792
Bulk Density	0.47 g/ml	PLUSS [®] method
Bonded Glycidyl Methacrylate	High (%)	PLUSS [®] method

Mechanical	Typical Value (SI)	Test Method
Tensile Strength	6 MPa	ASTM D638/2010
Percentage Elongation	>1000 %	ASTM D638/2010
Tensile Modulus	0.57 MPa	ASTM D638/2010
Flexural Modulus	17 MPa	ASTM D790/2010
Flexural Strength	1.70 MPa	ASTM D790/2010

Pluss Advanced Technologies Pvt. Ltd.

B-205, Tower B – Pioneer Urban Square, Sec 62, Gurugram-122008, Haryana, India

Telephone: +91 - 124 - 4309490/91/92

E-mail: info@pluss.co.in | Web: www.pluss.co.in

Page 1 of 2 Doc: 136, July, 2020

Hardness	Typical Value (SI)	Test Method		
Durometer Hardness				
Shore A	60	ASTM D2240/2004		
Shore D	10	ASTM D2240/2004		

Thermal	Typical Value (SI)	Test Method
Vicat Softening Temperature	50 °C	ASTM 1525/2010

Storage and Handling Procedures

OPTIM® GE-344 should be stored in a dry, cool and well-ventilated area. It is recommended that prior to processing, the requisite quantity of material to be used should be dried in a hopper dryer or oven at 50-60 °C for about 2 hours for obtaining best results. Read and understand Safety Data Sheet (SDS) for more detailed information on the safe handling and disposal of these speciality polymers.

Processing Conditions

OPTIM® GE-344 can be added to polycarbonates & polyesters to achieve good dispersion of fillers within the polymer matrix thereby obtaining best properties. It is recommended to purge the equipment thoroughly after a run is completed as OPTIM® GE-344 tends to crosslinks when kept for long periods at high temperatures. Maximum processing temperature should not generally exceed 290 °C.

Packaging

OPTIM® speciality polymers are supplied in pre-dried form in 25 Kg (55 lbs) PE lined, HD woven sack-laminated paper bags and 750 Kg (1650 lbs) FIBC's. Depending upon customer's requirement, the bags can be further palletized for dispatch. They should be stored in cool and dry place.

The information given here is meant as a guide to determining suitability of our products for the stated applications. It is based on trials carried out by our laboratories and data selected from literature and shall in no event be held to constitute or imply any warranty. The products are intended for use in industrial applications. The users should test the materials before use and satisfy themselves with regard to contents and suitability in the desired application. Our formal specifications define the limits of our commitment. Recommendation herein may not be construed as freedom to infringe/operate under any third party patents. In the event of a proven claim, our liability is limited only to replacement of our material and in no case shall we be liable for special, incidental or consequential damages arising out of usage of our material. This datasheet is subject to change without notice.

Page 2 of 2 Doc: 136, July, 2020